

# Prophy-Mate neo



## Air Powered Tooth Polishing System

Enhanced Prophy-Mate neo unites form and functionality for easier use. Excellent weight balance and a lightweight, compact powder chamber make Prophy-Mate neo comfortable to hold, while the original NSK handpiece connection swivels 360° even under strong air pressure. Effortless operation shortens time for treatment of plaque and stains. 60° and 80° nozzles are available.



### Ergo-Comfort Design

Lightweight, compact design and well-considered weight balance enable easy handling for minimised hand and wrist fatigue, helping to ensure thorough treatment.



### Smooth, Easy 360° Swivel

Twin joints rotate smoothly 360° degrees for easy operability, responding flexibly to minute fingertip movements with effortless adjustment of the nozzle angle.



### Simple One-touch Connection

The Prophy-Mate neo is designed for a one-touch attachment to NSK couplings and other major coupling brands. The handpiece also can be attached to the powder case with one-touch operation.



### Improved Polishing Power

With NSK original twin nozzles, greater polishing power is realized. With powerful jet, cleaning time is greatly shortened thus reduces treatment time.



### Easy Detachable Nozzles with 60° and 80°

Selectable 60° and 80° nozzles maximise the cleaning ability. 80° nozzle works especially well for molar area and occluding surface and 60° nozzle for anterior tooth.



# FLASH pearl CLEANING POWDER


## Sparkling Results Every Time

FLASH pearl, a cleaning powder for Prophy-Mate neo, is a spherical particulate powder designed to roll smoothly over tooth surfaces and penetrate all corners for rapid cleaning. The spherical shape of the powder granules lessens the likelihood of damage to teeth and soft tissue while removing stains and plaque quickly and safely.

\* Adverse reactions to this product are rare.



Spherical granules remove residues from every corner



FLASH pearl



Conventional Sodium Bi-Carbonate powder

MODEL FLASH pearl ORDER CODE Y900693

- Stylishly packaged in a handy original box.
- Contains 100 x 15g sachets



MODEL FLASH pearl (Bottle) ORDER CODE Y900698


- 4 bottles packaged in a box
- Comes with a measuring cup for your convenience
- Each bottle contains 300gms



FLASH pearl roll smoothly over tooth surfaces



No damage  
FLASH pearl avoids surface damage



Enamel damage  
Conventional Sodium Bi-Carbonate is aggressive

## Prophy-Mate neo Complete System

MODEL	ORDER CODE	PRODUCT	FOR
PMNG-PTL-P	Y135029		for NSK Coupling
PMNG-KV-P	Y135030		for KaVo® I-ED Coupling
PMNG-SR-P	Y135031		for Sirona® LCD Coupling
PMNG-WH-P	Y135032		for W&H® Roto Quick

MODEL	ORDER CODE	PRODUCT	FOR
PMNG-BA-P	Y135033		for Bio-Air® Unity®
PMNG-M4-P	Y135034		for Connect direct to the handpiece tubing M4/WLS1
PMNG-B2-P	Y135035		for Connect direct to the handpiece tubing BORDEN

Contents  
 • Handpiece with 60° nozzle head • Powder case • Replacement nozzle head 80°  
 • 5pcs. x 15g sachets of FLASH pearl cleaning powder • Maintenance kit

\*Couplings are not included

## Spare Parts

MODEL	PRODUCT	ORDER CODE	MODEL	PRODUCT	ORDER CODE	MODEL	PRODUCT	ORDER CODE
PMN-HIP	Handpiece with 60° nozzle head	T797010	Powder Case Cover		T798133	Blower Nozzle-WH (neo)		T888094
Nozzle 60°		T797012	Gasket		T798135	Blower Nozzle-BA (neo)		T889094
Nozzle 80°		T797013	O-ring Front nozzle		D0312039070	Blower Nozzle-M4 (neo)		T884094
PMNG-PTL	For NSK Coupling	T798020	O-ring Rear nozzle		D0312029070	Blower Nozzle-B2 (neo)		T885094
PMNG-KV	For KaVo® MULTITEX® LUX Coupling	T886020	PTL O-ring Set Pack of 5		Y900580	Lubrication Oil		Z016112
PMNG-SR	For Sirona® Quick Coupling	T887020	PM O-ring Set Pack of 3		Y900054	Cleaning Wire (L)		T798091
PMNG-WH	For W&H® Roto Quick Coupling	T888020	Ring Wrench		T797601	Cleaning Wire (S)		T798095
PMNG-BA	For Bio-Air® Unity® Coupling	T889020	Blower Nozzle-PTL (neo)		T798094	Cleaning File		T798092
PMNG-M4	For M4west 4 hole joint	T884020	Blower Nozzle-KV (neo)		T886094	Cleaning Brush		T798093
PMNG-B2	For Borden 2/3 hole joint	T885020	Blower Nozzle-SR (neo)		T887094			

\*Do not wash the powder case or the powder case's cap in a thermo-disinfector.

Washable in the thermodisinfector Autoclavable up to 135°C